

Category	Product	Maxim Part Number
Efficient Power	Buck	MAX38640AELT+
Efficient Power	Buck	MAX15026BETD+
Efficient Power	Boost	MAX17225ELT+
Efficient Power	Boost	MAX668EUB+
Efficient Power	Buck-Boost	MAX77827CEWC+T
Efficient Power	Buck-Boost	MAX77816CEWP+T
Efficient Power	LDO	MAX38902BATA+
Efficient Power	LDO	MAX1510ETB+
Efficient Power	Continua	MAX38888ATD+
Precision Measurement	ADC	MAX11410ATI+
Precision Measurement	ADC	MAX11168EUB+
Precision Measurement	DAC	MAX5541ESA+
Precision Measurement	DAC	MAX5715AAUD+
Precision Measurement	Audio Amp	MAX98357AEWL+ T
Precision Measurement	Audio Amp	MAX98390EWX+
Precision Measurement	Op-Amp	MAX40075AUT+T
Precision Measurement	Op-Amp	MAX40100ANT+
Precision Measurement	CSA	MAX44284EAUT+
Precision Measurement	CSA	MAX40201FAUA+
Rugged Connectivity	RS485	MAX14780EESA+T
Rugged Connectivity	RS485	MAX3485AEASA+
Rugged Connectivity	RS232	MAX13235EETP+
Rugged Connectivity	RS232	MAX33250EELC+
Rugged Connectivity	CAN	MAX13054AEASA+
Rugged Connectivity	CAN	MAX33054EASA+
Rugged Connectivity	BTR Switch	MAX14778ETP+T
Rugged Connectivity	BTR Switch	MAX14763ETA+T
Rugged Connectivity	Wireless	MAX41460GUB+
Rugged Connectivity	Wireless	MAX7034AUI+
Robust Protection	Supervisor	MAX16150BWT+
Robust Protection	Supervisor	MAX16140D220JM+
Robust Protection	Temp Sensor	MAX6680MEE+T
Robust Protection	Temp Sensor	MAX31875R0TZS+
Robust Protection	Isolation	MAX12930BASA+T
Robust Protection	Isolation	MAX22445FAWE+T
Robust Protection	Ideal Diode/Vref	MAX40203AUK+
Robust Protection	Ideal Diode/Vref	MAX6078AMWT25+T
Robust Protection	RTC	MAX31341BEWC+T
Robust Protection	RTC	DS3231MZ+