




FRONT VIEW



RIGHT VIEW



TOP VIEW



	THICKNESS	QTY	WIDTH	LENGTH	HEIGHT
	mm		mm	mm	mm
TOTAL DIMENSIONS	x	x	356	178	120
FRONT	6	1	356	6	120
BACK	6	1	356	6	120
TOP	6	1	356	166	6
SIDE	6	2	6	166	108
BOTTOM	6	2	100	166	6
BRACE	6	2	6	166	25
INNER WALL	6	2	6	166	20
BRACKET	8	1	168	166	8

M3 TAPPED HOLES