



24V +/-10%
V_{IN}

GND

V_{DD}

FAULT#

DIM IN

80V OUT max
LED+

LED-

START THRESHOLD = 20V

SWITCHING FREQUENCY = 300kHz

OUTPUT CAPS: EEU-ED2C470 (10x20)
PEAK CURRENT = 6A