


TOP VIEW



REFIN REFOUT SHREF PD G/T V<sub>DD</sub> V<sub>DD</sub> V<sub>DD</sub> OV<sub>DD</sub> DORA D13A D12A D11A D10A D9A D8A D7A

68 67 66 65 64 63 62 61 60 59 58 57 56 55 54 53 52

GND 1  
 INAP 2  
 INAN 3  
 GND 4  
 GND 5  
 COMA 6  
 REFAP 7  
 REFAN 8  
 GND 9  
 REFBN 10  
 REFBP 11  
 COMB 12  
 GND 13  
 GND 14  
 INBN 15  
 INBP 16  
 GND 17

51 D6A  
 50 D5A  
 49 D4A  
 48 D3A  
 47 D2A  
 46 D1A  
 45 D0A  
 44 DAV  
 43 OV<sub>DD</sub>  
 42 DORB  
 41 D13B  
 40 D12B  
 39 D11B  
 38 D10B  
 37 D9B  
 36 D8B  
 35 D7B

**MAX12557**

EXPOSED PADDLE (GND)

18 19 20 21 22 23 24 25 26 27 28 29 30 31 32 33 34

DIFFCLK/  
SECLK  
 CLKN  
 CLKP  
 DIV2  
 DIV4  
 V<sub>DD</sub>  
 V<sub>DD</sub>  
 V<sub>DD</sub>  
 V<sub>DD</sub>  
 OV<sub>DD</sub>  
 D0B  
 D1B  
 D2B  
 D3B  
 D4B  
 D5B  
 D6B

10mm x 10mm x 0.8mm THIN QFN