

Packet	Dir	Reset	Time
219	-->	49.877 ms	257.527 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors	Time
0	S	GET	0	0	GET_DESCRIPTOR	DEVICE type	0x0000	DEVICE Descriptor	23.905 ms

Packet	Dir	Reset	Time
461	-->	49.876 ms	254.770 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	wLength	Time
1	S	SET	0	0	SET_ADDRESS	New address 7	0x0007	0	34.630 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors	Time
2	S	GET	7	0	GET_DESCRIPTOR	DEVICE type	0x0000	DEVICE Descriptor	42.637 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors	Time
3	S	GET	7	0	GET_DESCRIPTOR	STRING type, LANGID codes requested	Language ID 0x0000	Lang Supported	12.221 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors	Time
4	S	GET	7	0	GET_DESCRIPTOR	STRING type, Index 1	Language ID 0x0409	Maxim	7.538 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors	Time
5	S	GET	7	0	GET_DESCRIPTOR	STRING type, Index 2	Language ID 0x0409	MAX3420E Enum Code	10.660 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors	Time
6	S	GET	7	0	GET_DESCRIPTOR	STRING type, Index 3	Language ID 0x0409	S/N 3420E	14.955 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors	Time
7	S	GET	7	0	GET_DESCRIPTOR	CONFIGURATION type, Index 0	0x0000	CONFIGURATION Descriptor	16.958 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors	Time
8	S	GET	7	0	GET_DESCRIPTOR	CONFIGURATION type, Index 0	0x0000	4 Descriptors	81.597 ms

Transfer	F	Control	ADDR	ENDP	bRequest	wValue	wIndex	Descriptors
9	S	GET	7	0	GET_DESCRIPTOR	STRING type, Index 4	Language ID 0x0409	MAX3420E/3421E Test Board