



**Input Signal**

- 1V<sub>p-p</sub> Y
- 0.7V<sub>p-p</sub> C
- DC-Biased Y and C

**Output Signal**

- 1V<sub>p-p</sub> Y
- 0.7V<sub>p-p</sub> C
- Two 1V<sub>p-p</sub> CVBSs
- AC- or DC-Coupled
- 3.3V Supply Rail

