



Input Signal

- 1V_{p-p} Y
- 0.7V_{p-p} C
- DC-Biased Y and C

Output Signal

- 1V_{p-p} Y
- 1V_{p-p} C
- AC- or DC-Coupled
- 3.3V Supply Rail

