



4/20/2008

RELIABILITY MONITOR REPORT  
FOR

**Cartridge Package**

**MAXIM Integrated Products**

120 San Gabriel Dr.  
Sunnyvale, CA 94086

This Report was prepared by  
Maxim Reliability Engineering

**Summary:**

The data in the tables that follow was generated as the result of an on-going Package Reliability Monitor. The specific assemblies included in this package monitor are:

ASSY SITE	PINS	PACKAGE		
Batangas Assembly	3	Cartridge	Batangas Assembly	2 Cartridge (Pb-Free)

Note: Due to the nature of the construction on this assembly, there is no operating life data collected.

The reliability data follows. At the start of this data is a description of the assembly vehicle used to generate this reliability data. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available. This report covers data between 4/1/2007 and 3/31/2008

---

**Assembly Information:**

Package Type: Cartridge  
Flammability: UL 94-V0  
Date Code Range: 0710 to 0710

---

**STORAGE LIFE**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	FA NO
STORAGE LIFE	0710	DS29022	70 C	336 HRS	77	0	
STORAGE LIFE	0710	DS29022	70 C	336 HRS	77	0	
STORAGE LIFE	0710	DS29022	70 C	336 HRS	77	0	
<b>Total:</b>						<b>0</b>	

---

**TEMPERATURE CYCLE**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	FA NO
TEMP CYCLE, 5' RAMP, 10' DWELL	0710	DS29022	0C TO 70C	300 CYS	77	0	
TEMP CYCLE, 5' RAMP, 10' DWELL	0710	DS29022	0C TO 70C	300 CYS	77	0	
TEMP CYCLE, 5' RAMP, 10' DWELL	0710	DS29022	0C TO 70C	300 CYS	77	0	
<b>Total:</b>						<b>0</b>	

---

**Assembly Information:**

Package Type: Cartridge (Pb-Free)  
Flammability: UL 94-V0  
Date Code Range: 0716 to 0716

---

**STORAGE LIFE**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	FA NO
STORAGE LIFE	0716	DSQ33G4	85 C	1000 HRS	77	0	
<b>Total:</b>						<b>0</b>	

---

**TEMPERATURE CYCLE**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	FA NO
-------------	-----------	--------------	-----------	-----------	----------	-------	-------

TEMP CYCLE, 5' RAMP, 10' DWELL	0716	DSQ33G4	-40 TO 85C	1000 CYS	77	0
<b>Total:</b>						<b>0</b>

---

**UNBIASED MOISTURE RESISTANCE**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	FA NO
MOISTURE SOAK	0716	DSQ33G4	60C/90% R.H.	1000 HRS	77	0	
<b>Total:</b>						<b>0</b>	