

MAX22505 EVK BOARD

P/N: MAX22505_EVK_BOARD

REV
4.0





maxim
integrated™

LAYER

TOP COMPONENT PLACEMENT

DATE:

ALL UNITS ARE IN 0.001"



MAX22505 EVK BOARD

P/N: MAX22505_EVK_BOARD

REV
4.0





maxim
integrated™

LAYER TOP SOLDER MASK

DATE:

ALL UNITS ARE IN 0.001"



MAX22505 EVK BOARD

P/N: MAX22505_EVK_BOARD

REV
4.0





maxim
integrated™

LAYER TOP COPPER

DATE:

ALL UNITS ARE IN 0.001"



MAX22505 EVK BOARD

P/N: MAX22505_EVK_BOARD

REV
4.0










maxim
integrated™

LAYER MID_LAYER 1

DATE:

ALL UNITS ARE IN 0.001"



MAX22505 EVK BOARD

P/N: MAX22505_EVK_BOARD

REV
4.0










maxim
integrated™

LAYER MID_LAYER 2

DATE:

ALL UNITS ARE IN 0.001"



MAX22505 EVK BOARD

P/N: MAX22505_EVK_BOARD

REV
4.0





maxim
integrated™

LAYER BOTTOM COPPER

DATE:

ALL UNITS ARE IN 0.001"



MAX22505 EVK BOARD

P/N: MAX22505_EVK_BOARD

REV
4.0





maxim
integrated™

LAYER BOTTOM SOLDER MASK

DATE:

ALL UNITS ARE IN 0.001"



MAX22505 EVK BOARD

P/N: MAX22505_EVK_BOARD

REV
4.0



maxim
integrated™

LAYER

BOTTOM COMPONENT PLACEMENT

DATE:

ALL UNITS ARE IN 0.001"

