




SDRMASKTOP_PG SDRMASKTOP_BG




ETCH TOP




L2_GND PLANE LAYER 2




ETCH_L3 LAYER 3




ETCH_L4 LAYER4




ETCH_L5 LAYER5




L6_V3V POWER PLANE LAYER 6




ETCH_L7LAYER 7




ETCH_L8 LAYER8




L9_GND PLANE LAYER 9



BOTTOM_ETCH



SDRMASKBOT_BG SDRMASKBOT_PG



HOLE CHART				
ALL UNITS ARE IN MILS				
FIGURE	SIZE	TOLERANCE	PLATED	QTY
.	4.0	+0.0/-4.0	PLATED	140
.	10.0	+0.0/-10.0	PLATED	9
.	10.0	+3.0/-10.0	PLATED	775
•	34.0	+2.0/-2.0	PLATED	1
•	36.0	+3.0/-3.0	PLATED	164
•	41.0	+3.0/-3.0	PLATED	61
▲	41.0	+3.0/-3.0	PLATED	17
•	42.0	+3.0/-3.0	PLATED	2
■	42.0	+3.0/-3.0	PLATED	19
•	42.0	+3.0/-3.0	PLATED	10
▲	48.0	+3.0/-3.0	PLATED	13
■	50.0	+3.0/-3.0	PLATED	9
c	71.0	+3.0/-3.0	PLATED	2
F	105.0	+3.0/-3.0	PLATED	2
G	120.0	+3.0/-3.0	PLATED	5
H	120.0	+3.0/-3.0	PLATED	3
■	40.0	+3.0/-3.0	NON-PLATED	9
L	47.0	+3.0/-3.0	NON-PLATED	2
N	61.0	+2.0/-2.0	NON-PLATED	2
P	130.0	+3.0/-3.0	NON-PLATED	2
Q	140.0	+3.0/-3.0	NON-PLATED	4

