

4/23/2015



**RELIABILITY MONITOR REPORT  
FOR**

**MFN 250V BCD (BCD250)**

**MAXIM INTEGRATED**

**160 RIO ROBLES  
SAN JOSE, CA 95134**

**This Report was prepared by  
MAXIM INTEGRATED Reliability Engineering**

**Summary:**

The data in the tables that follow was generated as the result of an on-going Process Reliability Monitor. The specific products in this process monitor are:

MAX14803CCM	MAX4811CTN+	MAX4811CTN+
-------------	-------------	-------------

The calculated failure rate for devices using this process is:

**FAILURE RATE: MTTF (YRS): 3256      QUANTITY: 100      FAILS: 0      FITS: 35.1**

The parameters used to calculate this failure rate are as follows:

**Cf: 60%      Ea: 0.7      Tu: 25 °C**

The reliability data follows and in this section is the detailed reliability data by stress. The reliability data section includes the latest data available. This report covers data between 4/1/2014 and 3/31/2015 .

**Process Information:**

Process Description: MFN 250V BCD (BCD250)

**OPERATING LIFE**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
HIGH TEMP OP LIFE	1422	MAX4811CTN+	135°C	168 HRS	100	0	NKUYB3075AL
<b>Total:</b>						<b>0</b>	

**STORAGE LIFE**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
STORAGE LIFE	1422	MAX4811CTN+	150°C	1000 HRS	80	0	NKUYB3075AL
<b>Total:</b>						<b>0</b>	

**TEMPERATURE CYCLE**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
TEMP CYCLE, 5' RAMP, 10' DWELL	1406	MAX14803CCM+	-65C TO +150C (Condition C)	1000 CYS	80	0	NRSWD2125A
TEMP CYCLE, 5' RAMP, 10' DWELL	1422	MAX4811CTN+	-65C TO +150C (Condition C)	500 CYS	80	0	NKUYB3075AL
<b>Total:</b>						<b>0</b>	

**TEMPERATURE HUMIDITY BIAS**

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
BIASED MOISTURE	1406	MAX14803CCM+	130C, 85% R.H.	100 HRS	34	0	NRSWD2125A
<b>Total:</b>						<b>0</b>	

**FAILURE RATE: MTTF (YRS): 3256      QUANTITY: 100      FAILS: 0      FITS: 35.1**