

8/1/2019



**RELIABILITY MONITOR REPORT
FOR**

MFN S5HV

MAXIM INTEGRATED

**160 RIO ROBLES
SAN JOSE, CA 95134**

**This Report was prepared by
MAXIM INTEGRATED Reliability Engineering**

Summary:

The data in the tables that follow was generated as the result of an on-going Process Reliability Monitor. The specific products in this process monitor are:

DG407DN+	MAX351ESE+
----------	------------

The calculated failure rate for devices using this process is:

FAILURE RATE: MTTF (YRS): 15115 QUANTITY: 78 FAILS: 0 FITS: 7.6

The parameters used to calculate this failure rate are as follows:

Cf: 60% Ea: 0.7 Tu: 25 °C

The reliability data follows and in this section is the detailed reliability data by stress. The reliability data section includes the latest data available. This report covers data between 4/1/2019 and 8/1/2019 .

Process Information:

Process Description: MFN S5HV

OPERATING LIFE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
HIGH TEMP OP LIFE	1813	MAX351ESE+	125°C	1000 HRS	78	0	NRLAG3711EX
Total:						0	

TEMPERATURE CYCLE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
TEMP CYCLE, 5' RAMP, 10' DWELL	1813	MAX351ESE+	-65C TO +150C (Condition C)	1000 CYS	80	0	NRLAG3711EX
TEMP CYCLE, 5' RAMP, 10' DWELL	1828	DG407DN+	-65C TO +150C (Condition C)	1000 CYS	80	0	NSZBHA593B
Total:						0	

TEMPERATURE HUMIDITY BIAS

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
BIASED MOISTURE	1813	MAX351ESE+	130C, 85% R.H.	96 HRS	80	0	NRLAG3711EX
BIASED MOISTURE	1828	DG407DN+	130C, 85% R.H.	96 HRS	80	0	NSZBHA593B
Total:						0	

UNBIASED MOISTURE RESISTANCE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
MOISTURE SOAK	1828	DG407DN+	130C, 85% R.H.	96 HRS	80	0	NSZBHA593B
Total:						0	

FAILURE RATE: MTTF (YRS): 15115 QUANTITY: 78 FAILS: 0 FITS: 7.6