

10/27/2017



**RELIABILITY MONITOR REPORT
FOR**

MFN M6HV

MAXIM INTEGRATED

**160 RIO ROBLES
SAN JOSE, CA 95134**

**This Report was prepared by
MAXIM INTEGRATED Reliability Engineering**

Summary:

The data in the tables that follow was generated as the result of an on-going Process Reliability Monitor. The specific products in this process monitor are:

DG201ACSE+	DG211CSE+
------------	-----------

The calculated failure rate for devices using this process is:

FAILURE RATE: MTTF (YRS): 46508 QUANTITY: 240 FAILS: 0 FITS: 2.5

The parameters used to calculate this failure rate are as follows:

Cf: 60% Ea: 0.7 Tu: 25 °C

The reliability data follows and in this section is the detailed reliability data by stress. The reliability data section includes the latest data available. This report covers data between 7/1/2017 and 9/30/2017 .

Process Information:

Process Description: MFN M6HV

OPERATING LIFE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
HIGH TEMP OP LIFE	1636	DG201ACSE+	135°C	1000 HRS	80	0	NRCAEA323AX
HIGH TEMP OP LIFE	1707	DG201ACSE+	135°C	1000 HRS	80	0	NRCAEA328DX
HIGH TEMP OP LIFE	1721	DG211CSE+	135°C	1000 HRS	80	0	NRCAEA331DX
Total:						0	

STORAGE LIFE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
STORAGE LIFE	1636	DG201ACSE+	150°C	1000 HRS	80	0	NRCAEA323AX
STORAGE LIFE	1707	DG201ACSE+	150°C	1000 HRS	80	0	NRCAEA328DX
STORAGE LIFE	1721	DG211CSE+	150°C	1000 HRS	80	0	NRCAEA331DX
Total:						0	

TEMPERATURE CYCLE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
TEMP CYCLE, 5' RAMP, 10' DWELL	1636	DG201ACSE+	-65C TO +150C (Condition C)	1000 CYS	80	0	NRCAEA323AX
TEMP CYCLE, 5' RAMP, 10' DWELL	1707	DG201ACSE+	-65C TO +150C (Condition C)	1000 CYS	80	0	NRCAEA328DX
TEMP CYCLE, 5' RAMP, 10' DWELL	1721	DG211CSE+	-65C TO +150C (Condition C)	1000 CYS	80	0	NRCAEA331DX
Total:						0	

TEMPERATURE HUMIDITY BIAS

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
-------------	-----------	--------------	-----------	-----------	----------	-------	---------

BIASED MOISTURE	1636	DG201ACSE+	130C, 85%	96	HRS	80	0	NRCAEA323AX
BIASED MOISTURE	1707	DG201ACSE+	130C, 85%	96	HRS	80	0	NRCAEA328DX
BIASED MOISTURE	1721	DG211CSE+	130C, 85%	96	HRS	80	0	NRCAEA331DX
					Total:		0	

FAILURE RATE: **MTTF (YRS): 46508** **QUANTITY: 240** **FAILS: 0** **FITS: 2.5**