

6/25/2020



**RELIABILITY MONITOR REPORT
FOR**

MFN C3

MAXIM INTEGRATED

**160 RIO ROBLES
SAN JOSE, CA 95134**

**This Report was prepared by
MAXIM INTEGRATED Reliability Engineering**

Summary:

The data in the tables that follow was generated as the result of an on-going Process Reliability Monitor. The specific products in this process monitor are:

MAX3222CUP+	MAX3232EUE+
-------------	-------------

The calculated failure rate for devices using this process is:

FAILURE RATE: MTTF (YRS): 46314 QUANTITY: 239 FAILS: 0 FITS: 2.5

The parameters used to calculate this failure rate are as follows:

Cf: 60% Ea: 0.7 Tu: 25 °C

The reliability data follows and in this section is the detailed reliability data by stress. The reliability data section includes the latest data available. This report covers data between 1/1/2020 and 3/31/2020 .

Process Information:

Process Description: MFN C3

OPERATING LIFE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
HIGH TEMP OP LIFE	1917	MAX3222CUP+	125°C	1000 HRS	80	0	JABA23658DX
HIGH TEMP OP LIFE	1931	MAX3222CUP+	125°C	1000 HRS	80	0	JABA2A664F
HIGH TEMP OP LIFE	1947	MAX3232EUE+	125°C	1000 HRS	79	0	J2DXBA723EX
Total:						0	

STORAGE LIFE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
STORAGE LIFE	1917	MAX3222CUP+	150°C	1000 HRS	80	0	JABA23658DX
STORAGE LIFE	1947	MAX3232EUE+	150°C	1000 HRS	80	0	J2DXBA723EX
Total:						0	

TEMPERATURE CYCLE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
TEMP CYCLE, 5' RAMP, 10' DWELL	1947	MAX3232EUE+	-65C TO +150C (Condition C)	500 CYS	80	0	J2DXBA723EX
Total:						0	

UNBIASED MOISTURE RESISTANCE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
MOISTURE SOAK	1947	MAX3232EUE+	130C, 85% R.H.	96 HRS	80	0	J2DXBA723EX
Total:						0	

FAILURE RATE: MTTF (YRS): 46314 QUANTITY: 239 FAILS: 0 FITS: 2.5