

6/25/2020



**RELIABILITY MONITOR REPORT
FOR**

MFN HV3

MAXIM INTEGRATED

**160 RIO ROBLES
SAN JOSE, CA 95134**

**This Report was prepared by
MAXIM INTEGRATED Reliability Engineering**

Summary:

The data in the tables that follow was generated as the result of an on-going Process Reliability Monitor. The specific products in this process monitor are:

MAX6035BAUR

The calculated failure rate for devices using this process is:

FAILURE RATE: MTTF (YRS): 15309 QUANTITY: 79 FAILS: 0 FITS: 7.5

The parameters used to calculate this failure rate are as follows:

Cf: 60% Ea: 0.7 Tu: 25 °C

The reliability data follows and in this section is the detailed reliability data by stress. The reliability data section includes the latest data available. This report covers data between 1/1/2020 and 3/31/2020 .

Process Information:

Process Description: MFN HV3

OPERATING LIFE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
HIGH TEMP OP LIFE	1915	MAX6035BAUR50+T	125°C	1000 HRS	48	0	NKR2C4075AB
HIGH TEMP OP LIFE	1915	MAX6035BAUR50+T	125°C	1000 HRS	31	0	NKR2C4075AB
Total:						0	

STORAGE LIFE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
STORAGE LIFE	1915	MAX6035BAUR50+T	150°C	1000 HRS	80	0	NKR2C4075AB
Total:						0	

TEMPERATURE CYCLE

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
TEMP CYCLE, 5' RAMP, 10' DWELL	1915	MAX6035BAUR50+T	-65C TO +150C (Condition C)	1000 CYS	80	0	NKR2C4075AB
Total:						0	

TEMPERATURE HUMIDITY BIAS

DESCRIPTION	DATE CODE	TEST VEHICLE	CONDITION	READPOINT	QUANTITY	FAILS	LOT NO.
BIASED MOISTURE	1915	MAX6035BAUR50+T	130C, 85% R.H. 96	HRS	40	0	NKR2C4075AB
BIASED MOISTURE	1915	MAX6035BAUR50+T	130C, 85% R.H. 96	HRS	40	0	NKR2C4075AB
Total:						0	

FAILURE RATE: MTTF (YRS): 15309 QUANTITY: 79 FAILS: 0 FITS: 7.5