



Ref. Certif. No.

US-18849-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE CERTIFICATS D'ESSAIS DES EQUIPEMENTS ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product
Produit

Component IC Current Limiter

Name and address of the applicant
Nom et adresse du demandeur

MAXIM INTEGRATED INC
160 RIO ROBLES
SAN JOSE, CA 95134 United States

Name and address of the manufacturer
Nom et adresse du fabricant

MAXIM INTEGRATED INC
160 RIO ROBLES
SAN JOSE, CA 95134 United States

Name and address of the factory
Nom et adresse de l'usine

MAXIM INTEGRATED PRODUCTS THAILAND) CO LTD
700//114 ARNATA NAKORN IND STATE, TAMBON
KLONG, TAMRU, MUANG DISTRICT, CHONBURI 20000
THAILAND

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{eme} page

Additional Information on page 2
See Page 2

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

None

Trademark (if any)
Marque de fabrique (si elle existe)
Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

Model / Type Ref.
Ref. De type

MAX14983E

Additional information (if necessary may also be reported on page 2)
Les informations complémentaires (si nécessaire,, peuvent être indiqués sur la 2^{eme} page

Additional Information on page 2

A sample of the product was tested and found to be in conformity with
Un échantillon de ce produit a été essayé et a été considéré conforme à la

IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1

As shown in the Test Report Ref. No. which forms part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de référence qui constitue partie de ce Certificat

E211395-A1-CB-1 issued on 2013-10-08

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2013-10-09
Original Issue Date: 2012-04-19

Signature:

Jolanta M. Wroblewska



Factories:

MAXIM PHILIPPINES OPERATING CORP
GATEWAY BUSINESS PARK,SPECIAL EXPORT PROCESSING ZONE,GENERAL TRIAS 4107 CAVITE
PHILIPPINES

Ratings:

(Electrical ratings is optional)

Input Voltage = 4.75 Vdc to 5.25 Vdc

Output Continuous Rating::MAX14983E = 55 mA

Output Current Limit::MAX14983E = 500 mA

Ambient = -40 to 85°C

This unit has two outputs; but only one output can be operated at a time. The select button on the Evaluation Board was used to switch between the two outputs.

Additional Information:

Correction 1 covers changes to Enclosure Id. 7-03 and change of Applicant and Manufacturer's address.

Additional information (if necessary)

Information complémentaire (si nécessaire)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2013-10-09

Original Issue Date: 2012-04-19

Signature:

Jolanta M. Wroblewska