

File E211395
Project 07CA53996

January 18, 2008

REPORT

on

COMPONENT - PROTECTORS, LOW VOLTAGE SOLID-STATE OVERCURRENT

Maxim Integrated Products
Sunnyvale, Ca

Recognized Company: Maxim Integrated Products

Copyright © 2008 Underwriters Laboratories Inc.

Underwriters Laboratories Inc. authorizes the above named company to reproduce this Report provided it is in its entirety.

Underwriters Laboratories Inc. authorizes the above named company to reproduce the latest pages of that portion of this Report consisting of this Cover Page through Page 4.

DESCRIPTION

PRODUCT COVERED:

*Component - Low voltage solid-state overcurrent protector Model MAX1558, **which** may be followed by **a combination of symbols, letters and/or numbers**.

GENERAL:

These devices are solid-state overcurrent protectors. They are solid-state switches that limit output current when the output load exceeds the current-limit threshold or when a load-side short-circuit is present. Solid-state overcurrent protectors are intended to be used on the load-side of an isolating transformer, power supply or battery to provide a means of supplementary protection.

NOMENCLATURE:

Example: MAX 1558 H ETB
 I II III

I - Model Designation
1558

II - Method of Activation
Null - Active Low
H - Active High

III - Packaging
ETB - Lead Free Packaging

ELECTRICAL RATINGS:

Model No.	Input Voltage Range, V dc	Number of Outputs	Operational Current Rating per Output, A	Overcurrent Protection Current Rating per Output, A peak
*MAX1558 Series	2.75-5.5	2	1.6 with R26Kohm external resistor maximum	2.6A @ 5.5V 1.45A @ 2.75V
*MAX1558 Series	2.75-5.5	2	1.6 with R39Kohm external resistor maximum	1.4A @ 2.75/5.5V
*MAX1558 Series	2.75-5.5	2	0.7 with R60Kohm external resistor minimum	0.9A @ 2.75/5.5V

Environmental Ratings

Maximum Ambient Temperature Rating: 85 °C

Storage Temperature Rating: -65 °C to 130 °C

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

For use only in complete equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.


Conditions of Acceptability -

1. These devices are integrated circuits and electrical spacings within the device are not specified.
2. These devices are entirely electronic in nature and have no means for manual operation or reset.
3. The terminals of these devices are for factory wiring only and are intended to be mounted on printed wiring board.
4. These devices have only been evaluated for supplementary overcurrent protection of secondary circuits supplied by the load side of a transformer or battery, and have not been evaluated for branch-circuit protection.
- *5. These devices have been investigated as electronic overcurrent protective devices in accordance with the requirements contained in **UL 2367, the Standard** for Solid State Overcurrent Protectors. As a result, use is permitted only on the load-side of an isolating transformer, power supply or battery with maximum levels limited as follows:

Output Voltage (V_{oc})		Output Current (I_{sc})	VA
V_{ac}	V_{dc}	A	(VxA)
≤ 20	≤ 20	$\leq 1000 / V_{oc}$	≤ 250
$20 < V_{oc} \leq 30$	$20 < V_{oc} \leq 30$	$\leq 1000 / V_{oc}$	≤ 250
—	$30 < V_{oc} \leq 60$	$\leq 1000 / V_{oc}$	≤ 250

Use on secondary supply circuits with a higher power capability requires additional evaluation for reliability, such as are contained in the Standard for Safety-Related Controls Employing Solid-State Controls, UL 991.

6. These devices limit currents to values less than the overcurrent protection rating of 5 amperes.
7. These devices have not been subjected Tests for Telecom applications and their suitability for connection to telecommunication networks with outside plant connections should be determined in the end-use.
8. These devices were evaluated with respect to continuous current operation at the current levels shown in the electrical ratings section of this report.
9. Suitable Capacitance shall be determined in preventing undervoltage conditions.
10. The unit is not suitable for use in outdoor applications
11. These devices were tested in the circuit shown below:



MARKING:

The Recognized Company, trade name, or trademark, catalog number, and Recognized Component Mark **RU** on the smallest package or reel.

Electrical ratings, including voltage range, maximum continuous current, protective current and operating temperatures shall be provided on the manufacturer's device specific datasheet. The datasheet may be web-based provided it is publicly accessible on the internet.

GENERAL CONSTRUCTION:

Spacings - No spacing requirements are specified.

Tolerance - Unless otherwise specified, all dimensions are nominal.

Corrosion Protection - All parts are of corrosion resistant material or are suitably plated to resist corrosion.

Current Carrying Parts - Stainless steel, silver, gold, nickel, aluminum, copper or copper alloy. May be plated with tin, lead, silver or gold.

*Insulated Housing - **Molded from Recognized Component (QMFZ2), high-pressure epoxy molding compound rated minimum 94V-2, RTI of 130°C.**

Refer to the following Ills. For overall view and dimensional information:

Model No.	Ill. No.
MAX1558/1558H	1