

12/3/2015



**PRODUCT RELIABILITY REPORT  
FOR**

**MAX31913**

**Maxim Integrated**

**14460 Maxim Dr.  
Dallas, TX 75244**

**Approved by:**

**Sokhom Chum  
MTS, Reliability Engineering**

**Conclusion:**

The following qualification successfully meets the quality and reliability standards required of all Maxim Integrated products:

MAX31913

In addition, Maxim Integrated's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maximintegrated.com/qa/reliability/monitor>.

**Device Description:**

A description of this device can be found in the product data sheet. You can find the product data sheet at <http://www.maximintegrated.com/search/parts.mvp>.

**Reliability Derating:**

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature  
tu = Time at use temperature (e.g. 55°C)  
ts = Time at stress temperature (e.g. 125°C)  
k = Boltzmann's Constant (8.617 x 10<sup>-5</sup> eV/°K)  
Tu = Temperature at Use (°K)  
Ts = Temperature at Stress (°K)  
Ea = Activation Energy (e.g. 0.7 eV)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7eV will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage  
Vs = Stress Voltage (e.g. 7.0 volts)  
Vu = Maximum Operating Voltage (e.g. 5.5 volts)  
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit  
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$\text{MTTF} = 1/\text{Fr}$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

**FAILURE RATE:**                      **MTTF (YRS):**            **10017**      **FITS:**            **11.4**  
**DEVICE HOURS:**            **80403110**      **FAILS:**            **0**

Only data from Operating Life or similar stresses are used for this calculation.

The parameters used to calculate this failure rate are as follows:

**Cf: 60%**            **Ea: 0.7**            **B: 0**            **Tu: 25 °C**            **Vu: 36 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. **Bold** Product Number denotes specific product data.

**Device Information:**

Process:                      Maxim SA Fab S45  
 Passivation:                SiN/SiO2  
 Die Size:                    87 x 95  
 Number of Transistors:  
 Interconnect:                Aluminum / 0.5% Copper  
 Gate Oxide Thickness:      140Å

**ESD HBM**

DESCRIPTION	DATE CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
ESD SENSITIVITY	1247 <b>MAX31913</b> ZJ386212AC	JESD22-A114 HBM 500 VOLTS	1	PUL'S	5	0
ESD SENSITIVITY	1247 <b>MAX31913</b> ZJ386212AC	JESD22-A114 HBM 1000 VOLTS	1	PUL'S	5	0
ESD SENSITIVITY	1247 <b>MAX31913</b> ZJ386212AC	JESD22-A114 HBM 1500 VOLTS	1	PUL'S	5	0
ESD SENSITIVITY	1247 <b>MAX31913</b> ZJ386212AC	JESD22-A114 HBM 2000 VOLTS	1	PUL'S	5	0
<b>Total:</b>					<b>0</b>	

**LATCH-UP**

DESCRIPTION	DATE CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
LATCH-UP V	1247 <b>MAX31913</b> ZJ386212AC	JESD78A, V-SUPPLY TEST 25C		3	0	
LATCH-UP I	1247 <b>MAX31913</b> ZJ386212AC	JESD78A, I-TEST 25C 100mA		6	0	
<b>Total:</b>					<b>0</b>	

**OPERATING LIFE**

DESCRIPTION	DATE CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
HIGH TEMP OP LIFE	0943 <b>MAX31190</b> WJ051035AB	125C, 3.6 VOLTS	192 HRS	45	0	

HIGH TEMP OP LIFE	1105	DS3920	ZJ163071AB	135C, 75V (V8)	192	HRS	77	0
HIGH TEMP OP LIFE	1218	MAX31910	ZJ276928FA	135C, 36V (V8)	192	HRS	80	0
HIGH TEMP OP LIFE	1231	MAX31865	ZJ381729AB-	125C, 3.7V (PSA)	192	HRS	80	0
HIGH TEMP OP LIFE	1247	<b>MAX31913</b>	ZJ386212AC	135C, 36V (V8)	192	HRS	80	0
HIGH TEMP OP LIFE	1323	DS3923	ZJ390843DA	125C, 3.6V (PSA) & 76.0V (PSD)	192	HRS	80	0
HIGH TEMP OP LIFE	1325	MAX34411	ZS386213CB	125C, 3.6 VOLTS	192	HRS	80	0
HIGH TEMP OP LIFE	1404	MAX31914	ZK410300AB	125C, 3.3V (PSA), 36 (PSD)	192	HRS	80	0
HIGH TEMP OP LIFE	1414	DS3922	ZJ486215BD	125C, 3.6V (PSA) & 76.0V (PSD)	192	HRS	79	0

**Total: 0**

**FAILURE RATE:                    MTTF (YRS):                    10017                    FITS:                    11.4**

**DEVICE HOURS:                    80403110                    FAILS:                    0**