

RELIABILITY REPORT  
FOR  
MAX1342BETX+  
(MAX1340/MAX1342/MAX1346/MAX1348)  
PLASTIC ENCAPSULATED DEVICES

April 9, 2009

**MAXIM INTEGRATED PRODUCTS**

120 SAN GABRIEL DR.  
SUNNYVALE, CA 94086

<b>Approved by</b>
Ken Wendel
Quality Assurance
Director, Reliability Engineering

## Conclusion

The MAX1342BETX+ successfully meets the quality and reliability standards required of all Maxim products. In addition, Maxim's continuous reliability monitoring program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards.

## Table of Contents

<b>I. ....Device Description</b>	<b>V. ....Quality Assurance Information</b>
<b>II. ....Manufacturing Information</b>	<b>VI. ....Reliability Evaluation</b>
<b>III. ....Packaging Information</b>	<b>IV. ....Die Information</b>
<b>.....Attachments</b>	

### I. Device Description

#### A. General

The MAX1340/MAX1342/MAX1346/MAX1348 integrate a multichannel, 12-bit, analog-to-digital converter (ADC) and a quad, 12-bit, digital-to-analog converter (DAC) in a single IC. The devices also include a temperature sensor and configurable general-purpose I/O ports (GPIOs) with a 25MHz SPI(tm)/QSPI(tm)/MICROWIRE(tm)-compatible serial interface. The ADC is available in a 4 or an 8 input-channel version. The four DAC outputs settle within 2.0 $\mu$ s, and the ADC has a 225ksps conversion rate. All devices include an internal reference (4.096V) providing a well-regulated, low-noise reference for both the ADC and DAC. Programmable reference modes for the ADC and DAC allow the use of an internal reference, an external reference, or a combination of both. Features such as an internal  $\pm 1^{\circ}\text{C}$  accurate temperature sensor, FIFO, scan modes, programmable internal or external clock modes, data averaging, and AutoShutdown(tm) allow users to minimize both power consumption and processor requirements. The low glitch energy (4nV&#149;s) and low digital feedthrough (0.5nV&#149;s) of the integrated quad DACs make these devices ideal for digital control of fast-response closed-loop systems. The devices are guaranteed to operate with a supply voltage from +4.75V to +5.25V. The devices consume 2.5mA at 225ksps throughput, only 22 $\mu$ A at 1ksps throughput, and under 0.2 $\mu$ A in the shutdown mode. The MAX1342/MAX1348 offer four GPIOs that can be configured as inputs or outputs. The MAX1340/MAX1342/MAX1346/MAX1348 are available in 36-pin thin QFN packages. All devices are specified over the -40 $^{\circ}\text{C}$  to +85 $^{\circ}\text{C}$  temperature range.

## II. Manufacturing Information

A. Description/Function:	12-Bit, Multichannel ADCs/DACs with FIFO, Temperature Sensing, and GPIO Ports
B. Process:	C6Y
C. Number of Device Transistors:	58131
D. Fabrication Location:	Japan
E. Assembly Location:	ASAT China, UTL Thailand
F. Date of Initial Production:	July 23, 2004

## III. Packaging Information

A. Package Type:	36-pin TQFN 6x6
B. Lead Frame:	Copper
C. Lead Finish:	100% matte Tin
D. Die Attach:	Conductive Epoxy
E. Bondwire:	Au (1.0 mil dia.)
F. Mold Material:	Epoxy with silica filler
G. Assembly Diagram:	#
H. Flammability Rating:	Class UL94-V0
I. Classification of Moisture Sensitivity per JEDEC standard J-STD-020-C	Level 1
J. Single Layer Theta Ja:	38°C/W
K. Single Layer Theta Jc:	1.4°C/W
L. Multi Layer Theta Ja:	28°C/W
M. Multi Layer Theta Jc:	1.4°C/W

## IV. Die Information

A. Dimensions:	164 X 166 mils
B. Passivation:	SiO <sub>2</sub> /SiN <sub>3</sub>
C. Interconnect:	Al/Cu
D. Backside Metallization:	None
E. Minimum Metal Width:	0.6um
F. Minimum Metal Spacing:	0.6um
G. Bondpad Dimensions:	5 mil. Sq.
H. Isolation Dielectric:	SiO <sub>2</sub>
I. Die Separation Method:	Saw

## V. Quality Assurance Information

- |                                   |   |
|-----------------------------------|---|
| A. Quality Assurance Contacts:    | Ken Wendel (Director, Reliability Engineering)<br>Bryan Preeshl (Managing Director of QA)       |
| B. Outgoing Inspection Level:     | 0.1% for all electrical parameters guaranteed by the Datasheet.<br>0.1% For all Visual Defects. |
| C. Observed Outgoing Defect Rate: | < 50 ppm  |
| D. Sampling Plan:                 | Mil-Std-105D  |

## VI. Reliability Evaluation

### A. Accelerated Life Test

The results of the 135°C biased (static) life test are pending. Using these results, the Failure Rate ( $\lambda$ ) is calculated as follows:

$$\lambda = \frac{1}{\text{MTTF}} = \frac{1.83}{192 \times 4340 \times 46 \times 2} \quad (\text{Chi square value for MTTF upper limit})$$

(where 4340 = Temperature Acceleration factor assuming an activation energy of 0.8eV)

$$\lambda = 23.3 \times 10^{-9}$$

$$\lambda = 23.3 \text{ F.I.T. (60\% confidence level @ 25°C)}$$

The following failure rate represents data collected from Maxim's reliability monitor program. Maxim performs quarterly 1000 hour life test monitors on its processes. This data is published in the Product Reliability Report found at <http://www.maxim-ic.com/>. Current monitor data for the C6Y Process results in a FIT Rate of 0.82 @ 25C and 14.21 @ 55C (0.8 eV, 60% UCL)

### B. Moisture Resistance Tests

The industry standard 85°C/85%RH or HAST testing is monitored per device process once a quarter.

### C. E.S.D. and Latch-Up Testing

The CO01-4 die type has been found to have all pins able to withstand a HBM transient pulse of +/-2500 V per JEDEC JESD22-A114-D. Latch-Up testing has shown that this device withstands a current of +/-250 mA.

**Table 1**  
Reliability Evaluation Test Results

**MAX1342BETX+**

TEST ITEM	TEST CONDITION	FAILURE IDENTIFICATION	SAMPLE SIZE	NUMBER OF FAILURES
<b>Static Life Test</b> (Note 1)	Ta = 135°C Biased Time = 192 hrs.	DC Parameters & functionality	46	0
<b>Moisture Testing</b> (Note 2) 85/85	Ta = 85°C RH = 85% Biased Time = 1000hrs.	DC Parameters & functionality	77	0
<b>Mechanical Stress</b> (Note 2) Temperature Cycle	-65°C/150°C 1000 Cycles Method 1010	DC Parameters & functionality	77	0

Note 1: Life Test Data may represent plastic DIP qualification lots.

Note 2: Generic Package/Process data